

OAKTON®

conductivity and conductivity/TDS/°C

CON 100 and CON 200

Push-button, customizable operating parameters lets you tailor meter functions to your specific application!

Both meters feature:

Five-point calibration

meter recalls previous calibration data

Reads conductivity from 0 to 199.9 mS across five ranges

Selectable automatic or manual temperature compensation

Manual or auto-ranging for conductivity measurements; auto-ranging for TDS readings

Memory function

stores and recalls 16 readings with corresponding temperature

Selectable cell constant (K)

K=1.0 for general applications; K=0.1 for pure water; K=10 for concentrated solutions

Selectable temperature coefficient

adjustable from 0 to 10% per °C for accurate compensation of almost any solution

Hold function, Error messages, selectable auto-off

Includes conductivity cell (K=1.0) with 3-ft cable

CON 200 also features:

Easily switches from conductivity to TDS readings

features an adjustable conductivity-to-TDS factor from 0.4 to 1.0

RS-232/printer output

download data to a computer or printer—ideal for GLP or HACCP data recording needs

Free OAKTON PC Datalog Assist Software on a 3.5" disk organizes data into format ready to import into most popular spreadsheet programs



ISO 9001
CERTIFIED

2 year
warranty
meter only

CE



Above: The CON 100 shown with conductivity cell.

Top right: Use a OAKTON printer with the CON 200 for hard copies of your readings.

Middle right: The CON 200 shown downloading readings into a computer.

Bottom right: Conductivity calibration kit contains all the components necessary for fast calibration and measurement in the field.

The OAKTON CON 100 and 200 meters let you customize operating parameters for your exact application! These meters offer high accuracy at an affordable price. Measure conductivity with the CON 100; measure both conductivity and TDS with the CON 200. The CON 200 also has RS-232/printer capabilities to output data to a computer or printer—ideal for GLP or HACCP data recording needs.

The advanced setup mode lets you check previous calibration data, activate Ready Indicator and Auto-off functions, select cell constant, select a conductivity-to-TDS conversion factor (CON 200 only), and more! Use built-in stand and optional AC adapter (order separately) for benchtop use. Probe cable wraps behind the meter for easy one-handed operation.

The conductivity calibration kit contains a variety of calibration standards in a hard carrying case that has space for your meter (order separately). See the back of this sheet for ordering information and complete specifications.

OAKTON® ...setting the standard, again and again™

Large LCD display clearly shows measurement mode, units and current function.



Cell holder positions cell for one-handed use or convenient storage.



Belt loop carrying case protects your meter from the elements while in use (order separately).



Portable printer provides hard copy of your readings anywhere in the field (sold separately).



Calibration solutions are available in economical bottles or TDS "Singles"—convenient pouches with a tear-off top.



Calibration kit contains the supplies you need for fast calibration and measurement in the field, all in a hard shell carrying case.



CON 100 and CON 200

• Applications •

General Applications: Monitor dissolved solids or conductivity levels quickly and easily in lab, field and educational environments.

Industrial Applications: Use for testing pollution controls, water treatment, and testing for water hardness. Also useful for checking cooling towers, boiler water, font solutions in printing operations, brines, swimming pools, whirlpools and rinse tanks.

Agricultural Applications: Use in aquariums, fish farms, hydroponics, and fertilizer/chemical concentrations.

• Specifications •

Mode	Conductivity	TDS (CON 200 only)	Temperature
Ranges	0.00 to 19.99 μ S (0.01 μ S); 0.0 to 199.9 μ S (0.1 μ S); 0 to 1999 μ S (1 μ S);	0.00 to 9.99 ppm (0.01 ppm); 10.0 to 99.9 ppm (0.1 ppm); 100 to 999 ppm (1 ppm);	Epoxy body cells: 0 to 80°C (0.1°C) Glass body cells: 0 to 100°C (0.1°C)
(Resolution)	0.00 to 19.99 mS (0.01 mS); 0.0-199.9 mS (0.1 mS)	1.00 to 9.99 ppt (0.01 ppt); 10.0-99.9 ppt (0.1 ppt) / 100-200ppt (1 ppt)	
Accuracy	\pm 1% full scale	\pm 1% full scale	\pm 0.5°C
Calibration	up to five points (one point per range)	up to five points (one point per range)	offset 0.1°C increments

Temperature compensation: Automatic or manual (selectable) from 0 to 50°C

Operating temperature: 0 to 50°C

Cell constant (K): 1.0, 0.1 or 10 selectable

Temperature coefficient: adjustable from 0.00 to 10.00% per °C

Memory: Stores up to 16 sets

Power: 4 x 1.5 V AAA batteries > 60 hours continuous use (included); 9 V, 500 mA AC adapter (optional)

Dimensions: Meter: 7.5"L x 3.5"W x 1.75"H (19 x 9 x 4.5 cm);

Boxed: 9.2"L x 9.2"W x 2.75"H (23 x 23 x 7 cm)

Weight: Meter: 1 lb (0.5 kg); Boxed: 2 lbs (0.9 g)

CON 200 meter only:

Conductivity-to-TDS factor: adjustable from 0.4 to 1.0

RS-232: 9 pin female, select baud rates 2.4, 4.8, 9.6 and 19.2 Kbps, stop bit, parity

Specifications for RS-232 output computer requirements:

386 and above (or compatible) with disk drive (1.44 MB). DOS 3.0 and above, RS-232 serial port, 430K RAM. Baud rate: 2.4, 4.8, 9.6 and 19.2 kbps selectable. Stop bit: 1 or 2 selectable. Parity: odd (1); even (2); or none (0) selectable. Meter's RS-232 Output Connector: 9 pin female.

• Ordering Information •

CON 100 and CON 200 Meters

All meters include conductivity cell WD-35607-50 (K=1.0), one probe holder, operating instructions and batteries. Shipping weight 2.0 lb (0.9 kg). CON 200 includes PC Datalog Assist Software on 3.5" disk.

WD-35607-10 CON 100 meter

WD-35607-20 CON 200 meter

Conductivity Cells

Cat. No.	Cell Constant	Body
WD-35607-50	1.0	Epoxy
WD-35607-55	0.1	Epoxy
WD-35607-51	10	Epoxy
WD-35607-52	1.0	Glass
WD-35607-56	0.1	Glass
WD-35607-53	10	Glass

WD-35607-57 Conductivity cell, stainless steel body and sensor (K = 1.0). Removable guard for easy cleaning

WD-35607-54 Flow-through conductivity cell, glass body/platinum sensor (K = 1.0). For continuous in-line measurement for flows up to 1 gal/min 100 mm L x 22 mm dia with 10-ft cable. Shpg wt 0.4 lb (0.2 kg)

Accessories

WD-35615-75 Portable meter carrying case. Protects meter while still letting you take measurements—case's top and side openings let probe and probe connections remain accessible. Shpg wt 1 lb (0.5 kg)

WD-35615-07 AC adapter, 9 VDC to 110 VAC. Shpg wt 1.3 lbs (0.6 kg)

WD-35615-08 AC adapter, 9 VDC to 220 VAC. Shpg wt 1.3 lbs (0.6 kg)

WD-35607-69 Calibration kit contains four each of TDS "Singles" calibration solution pouches 447 μ S, 1413 μ S, 2764 μ S, and 15.0 mS and four rinse water pouches, all in a hard plastic carrying case with room for your meter. Dimensions: 11.5"L x 14"W x 3"H. Shpg wt 1.5 lbs (0.7 kg)

Calibration solutions

Catalog number	Calibration solution type	Conductivity-to-TDS conversion factors		
		ppm KCl	ppm NaCl	ppm 442
WD-35653-10	447 μ S	225.6	215.5	300.0
WD-35653-11	1413 μ S	744.7	702.1	1000
WD-35653-12	2764 μ S	1382	1414.8	2062.7
WD-35653-13	15,000 μ S	8759	8532	13,455

Calibration solution pouches. box of 20. Each pouch contains 20 ml of premixed calibration solution. Since the pouches are individually sealed, the solution is guaranteed to be fresh and contaminant free every time. Accuracy \pm 1% at 25°C. Shpg wt 1 lb (0.5 kg)

WD-00653-23	23 μ S	11.6	10.7	14.74
WD-00653-16	84 μ S	40.38	38.04	50.50
WD-00653-47	447 μ S	225.6	215.5	300.0
WD-00653-18	1413 μ S	744.7	702.1	1000
WD-00653-15	1500 μ S	757.1	737.1	1050
WD-00653-27	2070 μ S	1045	1041	1500
WD-00653-20	2764 μ S	1382	1414.8	2062.7
WD-00653-89	8974 μ S	5101	4487	7608
WD-00606-10	12,880 μ S	7447	7230	11,367
WD-00653-50	15,000 μ S	8759	8532	13,455
WD-00653-32	80 mS	52,168	48,384	79,688

Calibration solution bottles. 1 pint of premixed calibration solution in recyclable-PE bottle. Accuracy \pm 1% at 25°C. Shpg wt 1.1 lbs (0.5 kg).

WD-00653-23	23 μ S	11.6	10.7	14.74
WD-00653-16	84 μ S	40.38	38.04	50.50
WD-00653-47	447 μ S	225.6	215.5	300.0
WD-00653-18	1413 μ S	744.7	702.1	1000
WD-00653-15	1500 μ S	757.1	737.1	1050
WD-00653-27	2070 μ S	1045	1041	1500
WD-00653-20	2764 μ S	1382	1414.8	2062.7
WD-00653-89	8974 μ S	5101	4487	7608
WD-00606-10	12,880 μ S	7447	7230	11,367
WD-00653-50	15,000 μ S	8759	8532	13,455
WD-00653-32	80 mS	52,168	48,384	79,688

RS-232 Computer/Printer Accessories (for the CON 200 only)

WD-35622-00 Portable printer, 110 VAC, rechargeable, Shpg wt. 2 lbs (0.9 kg)

WD-35622-05 Portable printer, 220 VAC, rechargeable, Shpg wt. 2 lbs (0.9 kg)

WD-35615-09 Computer cable, 9-pin male. Shpg wt. 0.2 lbs (0.1 kg)

WD-35622-59 Printer cable, 25-pin. Shpg wt. 0.2 lbs (0.1 kg)

• ORDER FROM •